



<p><b>AP 484</b></p> <p>S=0,95 cm<sup>2</sup> M=0,257 kg/m D=27,3 mm</p> <p><b>Upper crossbar (top border)</b></p>	
<p><b>AP 485</b></p> <p>S=0,93 cm<sup>2</sup> M=0,252 kg/m D=62,3 mm</p> <p><b>Lower guide</b></p>	
<p><b>AP 486</b></p> <p>S=1,504 cm<sup>2</sup> M=0,407 kg/m D=41,4 mm</p> <p><b>Open handle</b></p>	
<p><b>AP 487</b></p> <p>S=1,486 cm<sup>2</sup> M=0,403 kg/m D=41,37 mm</p> <p><b>Closed handle</b></p>	
<p><b>AP 574</b></p> <p>S=1,626 cm<sup>2</sup> M=0,441 kg/m D=42,71 mm</p> <p><b>Open handle</b></p>	
<p><b>AP 607</b></p> <p>S=2,034 cm<sup>2</sup> M=0,551 kg/m D=45,5 mm</p> <p><b>Closed handle</b></p>	

<p><b>AP 609</b></p> <p>S=1,13 cm<sup>2</sup> M=0,306 kg/m D=63 mm</p> <p><b>Lower guide</b></p>	
<p><b>AP 616</b></p> <p>S=0,779 cm<sup>2</sup> M=0,211 kg/m D=35,8 mm</p> <p><b>Open handle</b></p>	
<p><b>AP 617</b></p> <p>S=0,412 cm<sup>2</sup> M=0,112 kg/m D=25,7 mm</p>	
<p><b>AP 618</b></p> <p>S=1,267 cm<sup>2</sup> M=0,343 kg/m D=55,9 mm</p> <p><b>Lower guide</b></p>	
<p><b>AP 619</b></p> <p>S=2,81 cm<sup>2</sup> M=0,761 kg/m D=91,0 mm</p> <p><b>Top guide</b></p>	
<p><b>AP 694</b></p> <p>S=1,852 cm<sup>2</sup> M=0,502 kg/m D=57,4 mm</p> <p><b>Lower crossbar (bottom border)</b></p>	